



Uygulamalar

Cerrahi Skarlar

Stress Urinary Incontinence

Gözenek

Labium Whitening

Cilt Yenileme

Relaxed Vagina

Akne Skarları

Dyspareunia

Kırışiklık

Colpoxerosis

Lekeler

Sexual Satisfaction

ESTETİK

JİNEKOLOJİK

CO2

CO2

FRAKSİYONEL

FRAKSİYONEL

Wavelength:	10600nm
Laser apparatus:	Sealed off laser device simulated by direct current
Optical beam quality:	TEM00
Output power:	30w
Spot size:	0.02~0.05mm <sup>2</sup>
Aiming beam:	Red semiconductor laser (635nm, less than 5mw)
Beam transport device:	Articulated arm with 7-joint and balance weight
Working mode:	Continuous operation
Output Mode:	Continuous, single pulse, interval pulse and super pulse
Scan scope:	Max 20mmx20mm
Scan graphics:	Circle, triangle, square, rectangle, hexagon, ellipse, line
Scanning Mode:	Random, Normal and Midsplit scan
Scanning speed:	More than 10m/s
Energy:	1- 30W
Distance:	0.1-2.6mm
Cooling system:	air circulation
Weight:	40kg
Dimension:	65*48*117cm
Power:	220V/11V

